



Tab material: Isotan (54%Cu,44%Ni,Mn)

All framed values will be used for dimension checking !

- Samples can deviate in the execution from the serie.

- Dimensions and tolerances can be specified only after the testing of the devices for the mass production definitely

| | | | | | | | | | | | |
|---------------------------------|-----------------------|--|--|--------------------------------|-----------------------|--|--|---------------------|----------|----------|-----|
| Rev. | <input type="radio"/> | | | Rev. | <input type="radio"/> | | | Customer's Approval | | | |
| Rev. | <input type="radio"/> | | | Rev. | <input type="radio"/> | | | Date | | | |
| Rev. | <input type="radio"/> | | | Rev. | <input type="radio"/> | | | Signature | | | |
| Titel: CR2032 MFR AH1 | | | | | | | | Scale 2:1 | Drawn | 24.11.06 | SRi |
| | | | | | | | | | Checked | 30.11.06 | BBö |
| | | | | | | | | | Approved | | |
| renata batteries | | | | CH-4452 Itingen Switzerland | | | | 3.9167.4- | | | |